



CRIMP CHART

Hose	Stem	Ferrule	-04 (1/4")	-05 (5/16")	-06 (3/8")	-08 (1/2")	-10 (5/8")	-12 (3/4")	-16 (1")	-20 (1-1/4")	-24 (1-1/2")	-32 (2")	-40 (2-1/2")	-48 (3")	-64 (4")
Low/Medium Pressure	C5CXH	G	-	18.30	20.45	22.50			35.30	44.95					
		GS	GS1F-4				27.70	31.85							
	C5C and C5CXH are "non true bore" hoses, please consult the catalogue for stem selection.														
	CR1	C	CN1	17.40		20.50	23.50	26.60	30.60	38.50					
		G	-	17.90		21.60	25.15	28.60	34.05	44.45					
	G1	G	-							52.05					
		GS	GS1F-2							49.80					
		GSP	GSP1F-2								58.40	71.10			
	G1H	G	-	18.30		21.45	25.90	28.85	34.30	44.70	52.05				
		GS	GS1F-2					26.80	32.25	40.65	49.80				
		GSP	GSP1F-2								58.40	71.10			
	GTH	G	-	19.05	20.05	21.60	26.30	29.30	35.30	43.45					
	MegaTech 500	GSP	GSP1F-2								57.40	70.60			
		GL	-								48.65	61.20	71.10	86.60	
	MegaTech 1000	G	-	17.80		20.60	24.90	29.50	33.70	43.20	51.30				
High Pressure	ACP (MegaTech II)	G	-							53.95					
		GSP	GSP1F-2								59.95	72.90			
	CM2TDL	G	-	18.15		21.85	26.30								
		GS	GS1F-2			20.70									
	CR2	C	CN2	18.90		21.80	24.40	27.60	31.70	39.50					
		G	-	18.80		22.60	26.65	29.70	35.45	45.20					
	EFG3K	GSP	GSP1F-4								62.00	74.55			
	G2	G	-							53.95					
		GS	GS1F-2							51.80					
		GSP	GSP1F-2								60.05	72.90			
	G2H	G	-							53.95					
		GS	GS1F-2							51.80					
		GSP	GSP1F-2								60.05	72.90			
	G2XH	G	-	18.80		22.60	26.65	29.70	35.45	44.70	53.95				
		GS	GS1F-2			21.35	23.9	27.45	33.00	41.40	51.80				
		GSP	GSP1F-2								60.05	72.90			
	M2T	G	-	18.15	20.20	21.85	26.30	28.60	34.80	43.45	49.80				
		GS	GS1F-2			20.70	23.00	27.20	32.75	38.35					
	M3K	G	-	17.80	20.05	20.55	25.40	29.70	35.45	45.70					
		GS	GS1F-2				22.75	27.45	33.00	40.90					
	MXT	G	-	18.15	20.20	21.20	25.15	28.85	34.30	42.80					
		GS	GS1F-2			20.20	23.00	26.55	31.50	38.75					
	MXT-XTP	G	-	18.15	20.20	20.90	25.15	28.85	34.30	42.80					
		GS	GS1F-2			20.20	23.00	26.55	31.50	38.75					
Very High Pressure	EFG4K	GS	GS1F-4			24.90	27.45	33.55	37.60	44.45	52.05				
	EFG6K	GS	GS1F-4			24.90	27.45	33.55	37.60	44.45					
		GS	GS1F-6							56.65					
		GSM	-								63.75	79.25			
	MXG4K-XTP	G	-		21.45	25.90	29.20	34.80							
		MXG4K-XTP with MegaCrimp Couplings is rated to 600,000 impulse cycles. Use MXG4K-XTP with GS Couplings for 1,000,000 impulse cycle rating													
		GS	GS1F-2			20.70	23.20	27.70	33.25						
		GS	GS1F-4						43.95						
	MXG5K-XTP	G	-		22.00	26.15									
		MXG5K-XTP with MegaCrimp Couplings is rated to 600,000 impulse cycles. Use MXG5K-XTP with GS Couplings for 1,000,000 impulse cycle rating													
		GS	GS1F-2			21.00	23.85		33.25						
		GS	GS1F-4						44.85						
Specialty	GMV MegaFlex	GS	GSID1F-4				30.50								
		G	-					37.15	44.00	51.00					
		GSP	GSP1F-2								57.05	70.65			
	J2AT	GL											72.40	87.40	114.35
		G		18.80		22.75									
		GS	GS1F-2			21.35									
	PW6000	G	-			21.20									
	RFS	G	-	17.90		21.45	25.65		34.30	44.70					
	STH	CT		12.40		16.60	20.40	22.50	26.72	32.87					